

## Datasheet

### RPP30 polyclonal antibody (A01)

**Catalog Number:** H00010556-A01

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse polyclonal antibody raised against a partial recombinant RPP30.

**Immunogen:** RPP30 (NP\_006404, 169 a.a. ~ 268 a.a) partial recombinant protein with GST tag.

**Sequence:**

TISSALNLMQICKGKNVISSAAERPLEIRGPYDVANLGL  
LFGLSESDAKAAVSTNCRAALLHGETRKTAFGIISTVKK  
PRPSEGDEDCLPASKKAKCEG

**Host:** Mouse

**Reactivity:** Human

**Applications:** ELISA, WB-Ce, WB-Re, WB-Tr  
(See our web site product page for detailed applications information)

**Protocols:** See our web site at  
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Storage Buffer:** 50 % glycerol

**Storage Instruction:** Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 10556

**Gene Symbol:** RPP30

**Gene Alias:** FLJ38491, TSG15