

## Datasheet

### SIVA purified MaxPab mouse polyclonal antibody (B01P)

**Catalog Number:** H00010572-B01P

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse polyclonal antibody raised against a full-length human SIVA protein.

**Immunogen:** SIVA (AAH34562, 1 a.a. ~ 110 a.a)  
full-length human protein.

**Sequence:**

MPKRSCPFADVAPLQLKVRVSQRELSRGVCAERYSQ  
EVFDPSGVASIACSSCVRPVDGKAVCGQCERALCGQ  
CVRTCWGC GSVACTLCGLVDCSDMYE KVLCTSCAMF  
ET

**Host:** Mouse

**Reactivity:** Human

**Applications:** IF, WB-Tr

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Storage Buffer:** In 1x PBS, pH 7.4

**Storage Instruction:** Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 10572

**Gene Symbol:** SIVA1

**Gene Alias:** CD27BP, SIVA, Siva-1, Siva-2

**Gene Summary:** This gene encodes a protein with an important role in the apoptotic (programmed cell death) pathway induced by the CD27 antigen, a member of the tumor necrosis factor receptor (TNFR) superfamily. The CD27 antigen cytoplasmic tail binds to the N-terminus of this protein. Two alternatively spliced transcript variants encoding distinct proteins have been described.  
[provided by RefSeq]