

# ISOSLIDE® control slides

## Ensure the validity of your histological staining procedures

Test now and see yourself  
ISOSLIDE® control slides

### Is the stain positive or negative?

With high quality ISOSLIDE® control slides, you will have no question about the validity of your histological staining procedures. Simply compare your preparations with the control tissue specimens to be sure of your results.

### You're in control.




Each ISOSLIDE® box contains 25 slides with a paraffin-embedded section of animal tissue. One slide is prestained and serves as a positive control. The 24 remaining slides are to be stained according to either the accompanying Merck Millipore reference method, or your laboratory's own procedures. After staining, control slides are compared with laboratory material and the positive control to verify staining results.

### Certified quality in every box.

ISOSLIDE® products are CE certified, IVD registered, and come with comprehensive documentation. So they not only support our investigation, but also streamline lab accreditation and audits. For further security, all the slides in one box are produced from the same block of animal tissue.

### Your advantages

- Safe: Positive control for greater diagnostic security
- Convenient: Easy comparison with own samples and procedures
- Accurate: Proper identification of target structures
- Consistent: All slides in a box are from the same block of animal tissue
- Documented: Complete documentation for lab accreditation and audits/IVD registered and CE certified



# ISOSLIDE® control slides



Item	Description
1.02472.0001	ISOSLIDE® Warthin-Starry (25 pcs)
1.02560.0001	ISOSLIDE® AFB (25 pcs)
1.02561.0001	ISOSLIDE® Congo red (25 pcs)
1.02473.0001	ISOSLIDE® Methenamine (25 pcs)
1.00408.0001	ISOSLIDE® PAS (25 pcs)
1.00425.0001	ISOSLIDE® Alcian blue (25 pcs)
1.00361.0001	ISOSLIDE® Reticulin (25 pcs)
1.00380.0001	ISOSLIDE® Iron (25 pcs)

For further information please contact your local distribution partner:



For further information on Merck Millipore and our products contact:

Merck KGaA  
64293 Darmstadt, Germany  
[www.merckmillipore.com](http://www.merckmillipore.com)

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of their parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.