




CCR5 Antibody [T21/8]

CATALOG NUMBER: 51-348



Immunohistochemistry of human tonsil tissue stained using CCR5 Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, FACS, IHC, IP, WB
APPLICATIONS:	CCR5 antibody can be used in Western Blot starting at 1 - 3 ug/mL, and immunohistochemistry starting at 20 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Human CCR5
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Affinity Purified
PHYSICAL STATE:	Liquid
BUFFER:	Aqueous buffer, 0.09% sodium azide, may contain carrier protein/stabilizer
STORAGE CONDITIONS:	CR5 antibody should be stored long term (months) at -20 °C and short term (weeks) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	CCR5, C-C chemokine receptor 5, CD195 antigen, CD195, C-C CKR-5, Chemokine c-c motif receptor 5, Chemr13, CMKBR5, CKR5, Cc chemokine receptor 5, CCCR5, CCR-5, Ccr5 receptor, Chemokine receptor CCR5, HIV-1 fusion coreceptor, IDDM22, C-C chemokine receptor type 5, CC-CKR-5, CKR-5
ACCESSION NO.:	P51681
PROTEIN GI NO.:	1705896
OFFICIAL SYMBOL:	CCR5
GENE ID:	1234

FOR RESEARCH USE ONLY

December 13, 2016