




TNF Antibody [MAb1]

CATALOG NUMBER: 51-353



Immunohistochemistry of human liver tissue stained using TNF Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IHC
APPLICATIONS:	TNF antibody can be used in Western Blot, and immunohistochemistry starting at 10 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	Human TNF
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Affinity Purified
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2, 150 mM sodium chloride, 0.09% sodium azide
STORAGE CONDITIONS:	Store TNF antibody at 4 °C. As with all antibodies avoid freeze/thaw cycles
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,k
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	TNF, APC1 protein, Cachectin, DIF, TNF Alpha, Tumor necrosis factor-alpha, TNF-alpha, TNF-a, TNFA, Tumor necrosis factor, TNF, macrophage-derived, TNF, monocyte-derived, TNFSF2
ACCESSION NO.:	P01375
PROTEIN GI NO.:	135934
OFFICIAL SYMBOL:	TNF
GENE ID:	7124

Background

